

Injector Performance Table							
Injector Model				784			
Operating Pressure PSIG		Ozone Suction		Operating Pressure PSIG		Ozone Suction	
Injector Inlet	Injector Outlet	Motive Flow GPM	O3 Suction SCFH	Injector Inlet	Injector Outlet	Motive Flow GPM	O3 Suction SCFH
5	0	4.3	11.7	60	0	14.9	59.4
	1		9.9		5		57.5
	2		4.8		10		49.4
	3		2.2		15		44.1
	4		1.0		20		35.0
10	0	6.1	19.4		30		15.5
	2		15.7		35		10.4
	5		5.7		40		8.1
	7		2.0		45		4.9
	8		0.9		70		0
15	0	7.5	28.9	5		59.8	
	5		16.5	10		54.7	
	7		8.8	15		49.7	
	10		4.1	20		46.4	
	12		1.9	30		22.3	
20	0	8.6	33.8	40		13.5	
	5		21.3	45		9.8	
	10		8.1	50		7.6	
	12		5.0	55		4.2	
	15		2.4	80	0	61.0	
25	0	9.6	40.1		5	60.1	
	5		29.1		10	58.0	
	10		14.0		15	54.1	
	15		3.3		20	51.7	
	20		0.0		30	34.1	
30	0	10.6	48.2		40	18.4	
	5		32.6		50	11.7	
	10		20.3		60	6.3	
	15		9.6		65	3.5	
	20		4.2	90	0	62.0	
35	25	0.0	5		62.0		
	0	11.4	46.5		10	61.7	
	5		38.1		20	56.2	
	10		29.8		30	48.2	
	15		15.2		40	25.3	
20	8.2		50		16.5		
4000	25	12.2	4.1		60	11.0	
	0		12.9		53.0	70	5.7
	5				44.9	75	3.6
	10			35.9	100	0	62.0
	15			20.5		5	62.9
20	11.5	10		61.5			
25	7.1	20	58.3				
30	3.2	30	52.7				
45	0	12.9	56.5	40		35.7	
	5		48.2	50		20.9	
	10		38.6	60		14.6	
	15		29.1	70		9.6	
	20		15.0	80		5.0	
	25		9.5	120	0	63.4	
	30		6.0		5	63.6	
35	2.6	10	63.2				
50	0	13.6	58.2		20	62.6	
	5		52.0		30	57.3	
	10		43.1		40	55.1	
	15		35.8		50	34.5	
	20		20.4		60	22.6	
	25		13.6		70	16.7	
	30		9.3		80	11.8	
	35		6.0	90	7.3		
40	2.8	100	0.0				